

# MI HEATING CABLE SET ORDERING INFORMATION

Attach this form with the order and sent to nVent Customer Service Center

## Contact information

Customer name

Customer PO



**For pipe tracing applications, please submit TraceCalc Pro report print out.**

**For other applications or if Trace CalcPro report is not available please complete Section 1 & 2.**

## 1. These fields must be completed

**Heating cable set number:** e.g., A/61SA2200/40/538/208/7/12NS/X

**Maintain temperature**

°C

°F

**Approvals**

C-CSA-US

(all applicatios below except in conduit applications)

FM

(only applications with \*)

None

**Max. sheath temperature** (if known)

°C

°F

## 2a. Application must be selected

### Hazardous Locations

Industrial Pipe & Vessel Tracing (Dry/Damp) (5A/A)\*

Industrial Pipe & Vessel Tracing (Wet) (5B/A)\*

Snow Melting (2B/C)\*

Frost Heave Protection (1B/C)\*

Snow Melting in Conduit \*

Other. Please specify:

### Ordinary Location

Floor Warming (1B/C)

Snow Melting (2B/C)\*

Pool Deck Heating (2D/C)

Roof De-Icing (2E/B)

Non-Industrial Pipe and Vessel Tracing (Dry) (3A/A)\*

Non-Industrial Pipe and Vessel Tracing (Wet) (3B/A)\*

Non-Industrial Pipe and Vessel Tracing (Damp) (3C/A)\*

Industrial Pipe & Vessel Tracing (Dry/Damp) (5A/A)\*

Interior Pipe Tracing (Metal) (4A/D)

Interior Pipe Tracing (Non-Metallic) (4B/D)

Other. Please specify:

## 2b. Complete for hazardous location application

### Hazardous Location Classifications

Class	I
	II
	III
Division	1
	2
Group	A
	B
	C
	D
	E
	F
	G

T-Rating

### 3. Options

Reverse gland	1/2"	3/4"	1"	1-1/4"	
Pulling eye			Tail length (in)		Special length tolerance
Other	Please specify:				
Customer tag information (maximum 20 characters, including spaces)					
Technical support review					
Name (print)					
Signature:				Date	

### North America

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nvent.com



[nVent.com](https://www.nVent.com)

Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**