

TM20EX MECHANICAL THERMOSTAT

nVent RAYCHEM T-M-20-S/+x+y/EX is a mechanical surface sensing thermostat providing temperature control and temperature limit in hazardous areas. The safety limiter prevents the heating system from exceeding a preset maximum temperature should the control function fail to operate or an unsafe process temperature occur. Available in ranges: +0 °C +120 °C, +0 °C +200 °C and +50 °C +300 °C. The maximum rated voltage is 400 VAC. The switching current capacity is 16 A.

FEATURES

Simple to install and operate: supplied with 3 m long stainless steel fluid filled bulb and capillary, 6 cable entries

Energy saving, line-sensing electronic control thermostat

Adjustable set point temperature control: +0 °C +120 °C, +0 °C +200 °C and +50 °C +300 °C (with temperature limit ranges at +0 °C +120 °C, +50 °C +300 °C and +50 °C +300 °C respectively)

Direct switching, maximum current 16 A, 400 VAC: independent Ex d single pole change over micro switches with volt-free contacts

Lightweight unit, can be pipe mounted using nVent RAYCHEM support brackets or surface mounted

SPECIFICATIONS

Current Rating:	16 A
Depth:	90 mm
Height:	120 mm
Width:	220 mm
Max Voltage:	400 V
Material:	Glass Fiber Reinforced Polymer
Controller Switching Capacity:	Max 16 A @ 400 VAC, Resistive load
Thermostat Type:	Mechanical Thermostat

Catalog Number	Item Name	Controller Temperature Setting	Limiter Temperature Setting
1244-013410	T-M-20-S/+0+200C/EX	0 – 200 °C	50 – 300 °C
1244-013411	T-M-20-S/+50+300C/EX	50 – 300 °C	50 – 300 °C
1244-016536	T-M-20-S/+0+120C/EX	0 – 120 °C	0 – 120 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.