

GROUND ROD HEX DRIVING STUD FOR EXTERNALLY THREADED GROUND RODS



CERTIFICATIONS



FEATURES


Used in conjunction with threaded couplers while driving threaded ground rods

SPECIFICATIONS

Material: Steel

Catalog Number	Ground Rod Diameter, Nominal	Thread Size(TS)	Length(L)	Certifications
DS12	1/2"	1/2" UNC	38.100 mm	
DS58	5/8"	5/8" UNC	44.500 mm	RUS
DS34	3/4"	3/4" UNC	50.800 mm	RUS

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER