

## NVENT ERIFLEX ZIPFLEX SLEEVE



### CERTIFICATIONS



### FEATURES

Quick and easy screening

Installation tool included

Halogen free

### SPECIFICATIONS

Color:	Black
Material:	Polypropylene
Flammability Rating:	UL® 94HB
Working Temperature:	-30 to 140 °C

Catalog Number	Item Name	Diameter	Length	Unit Weight
ZFX100M8MMBK	554880	8 mm	100 m	0.015 kg
ZFX50M15MMBK	554890	15 mm	50 m	0.044 kg
ZFX30M20MMBK	554900	20 mm	30 m	0.070 kg
ZFX20M25MMBK	554910	25 mm	20 m	0.100 kg

## ADDITIONAL PRODUCT DETAILS

---

Unit weight is per meter (3.28').

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**