

# RESIDENTIAL & LIGHT COMMERCIAL - WINTER SAFETY PRODUCTS

## RAYCHEM FROSTGUARD PREASSEMBLED

- Roof and gutter de-icing (120 Vac only)
- Metal/plastic pipes, up to 2-1/2" in diameter
- Wet or Dry areas



- FrostGuard 120 V
- Plug-in heating cable with 6 foot cold lead and lighted 3-prong grounded plug
- Braid and jacket
- 6 W/ft @ 40°F



- FrostGuard 240 V
- 6 foot cold lead for hardwiring
- Braid and jacket
- 6 W/ft @ 40°F

## RAYCHEM WINTERGARD


- Metal/plastic pipes, up to 2" in diameter
- Dry areas only



- WinterGard 120 V
- Braid only
- 3 W/ft @ 40°F; 250 ft max. circuit

## RAYCHEM WINTERGARD PLUS

- Metal/plastic pipes, up to 6" in diameter
- Dry areas only



- WinterGard Plus 120 V
- Braid only
- 6 W/ft @ 40°F; 200 ft max. circuit



- WinterGard Plus 240 V
- Braid only
- 6 W/ft @ 40°F; 400 ft max. circuit

## RAYCHEM WINTERGARD WET

- Roof and gutter de-icing
- Metal/plastic pipes, up to 6" in diameter
- Wet or Dry areas




- WinterGard Wet 120 V
- Braid and jacket
- 6 W/ft @ 40°F; 200 ft max. circuit



- WinterGard Wet 240 V
- Braid and jacket
- 6 W/ft @ 40°F; 400 ft max. circuit

## RAYCHEM FROSTEX

- Metal/plastic pipes, up to 2" in diameter
- Dry areas only
- Residential use only



- Frostex 120 V
- Braid only
- 3 W/ft @ 50°F; 50 ft max. circuit

## RAYCHEM IN-PIPE

- Plastic pipes up to 1-1/4" in diameter
- **Mini** 120 V for insulated pipes up to 34 foot length
- **Miser** 120 V for insulated pipes up to 240 foot length
- **Retro** 120 V for uninsulated pipes up to 150 foot length
- **Retro** 240 V for uninsulated pipes up to 250 foot length



- In-Pipe 120 V
- Mini / Miser short lengths are stainless steel
- Miser long lengths are copper sheathed MI
- Miser has built-in ground-fault protection
- 4 W/ft Mini & Miser; 8 W/ft Retro



- In-Pipe Retro 240 V
- Copper sheathed MI
- Between 160 ft and 250 ft
- 8 W/ft

## RAYCHEM FREEZGARD

- Crankcase heater
- Fits compressors up to 5 HP or 40 inches in circumference



- FreezGard 120 V
- Braid and jacket



- FreezGard 208-277 V
- Braid and jacket

## RAYCHEM FROSTGUARD PREASSEMBLED

- Heating cable options ➡
- Accessories:
  - » For pipes: H903 application tape
  - » For roofs: H913/H914 roof clips; H915 downspout hanger
- Control options:
  - » TC-3 thermostatically controlled outlet

### FROSTGUARD 120 V

| Description | Catalog # |
|-------------|-----------|
| 6' Length   | FG1-6P    |
| 12' Length  | FG1-12P   |
| 18' Length  | FG1-18P   |
| 24' Length  | FG1-24P   |
| 36' Length  | FG1-36P   |
| 50' Length  | FG1-50P   |
| 75' Length  | FG1-75P   |
| 100' Length | FG1-100P  |

### FROSTGUARD 240 V

| Description | Catalog # |
|-------------|-----------|
| 6' Length   | FG2-6L    |
| 12' Length  | FG2-12L   |
| 18' Length  | FG2-18L   |
| 24' Length  | FG2-24L   |

## RAYCHEM WINTERGARD

- Heating cable options ➡
- Accessories:
  - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
- Control options:
  - » AMC-F5, AMC-1A, EC-TS

### WINTERGARD 120 V

| Description    | Catalog # |
|----------------|-----------|
| 100' TruckPak* | H311100   |
| 250' Reel      | H311250   |

\*WinterGard TruckPaks contains 100 feet of heating cable, two H900 Hardwire Power Connection Kits, one H910 Splice or Tee Kit, and one H903 roll of Application Tape.

## RAYCHEM WINTERGARD PLUS

- Heating cable options ➡
- Accessories:
  - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
- Control options:
  - » AMC-F5, AMC-1A, EC-TS

### WINTERGARD PLUS 120 V

| Description    | Catalog # |
|----------------|-----------|
| 50' Box        | H611050   |
| 100' TruckPak* | H611100   |
| 250' Reel      | H611250   |

### WINTERGARD PLUS 240 V

| Description    | Catalog # |
|----------------|-----------|
| 50' Box        | H621050   |
| 100' TruckPak* | H621100   |
| 250' Reel      | H621250   |

## RAYCHEM WINTERGARD WET

- Heating cable options ➡
- Accessories:
  - » For pipes: H900 hardwire or H908 plug-in power connection kit; H903 application tape; H910 Splice/Tee kit
  - » For roofs: H900 hardwire or H908 plug-in power connection kit; H913/H914 roof clips; H915 downspout hanger; H910 Splice/Tee kit
- Control options:
  - » AMC-F5, AMC-1A, EC-TS
  - » PD-Pro, GF-Pro, CIT-1, GIT-1, LCD-8

### WINTERGARD WET 120 V

| Description    | Catalog # |
|----------------|-----------|
| 50' Box        | H612050   |
| 100' TruckPak* | H612100   |
| 250' Reel      | H612250   |
| 500' Reel      | H612500   |
| 1000' Reel     | H6121000  |

### WINTERGARD WET 240 V

| Description    | Catalog # |
|----------------|-----------|
| 50' Box        | H622050   |
| 100' TruckPak* | H622100   |
| 250' Reel      | H622250   |
| 500' Reel      | H622500   |
| 1000' Reel     | H6221000  |

## RAYCHEM FROSTEX

- Heating cable options ➡
- Accessories:
  - » 9800 FlexFit plug kit; 9610 Application tape
- Control options:
  - » TC-3 thermostatically controlled outlet

### FROSTEX 120 V

| Description    | Catalog # |
|----------------|-----------|
| 50' TruckPak** | 5050      |
| 100' Reel      | 2102      |
| 250' Reel      | 2250      |
| 500' Reel      | 2502      |

\*\*Frostex TruckPaks contains 50 feet of Frostex Heating Cable, 2 each 9800 FlexFit Plug Kits, and 1 each 9610 Application Tape.

## RAYCHEM IN-PIPE

- Heating cable options ➡
- Control options:
  - » Built-in controller

### IN-PIPE 120 V


| Description      | Catalog #                     |
|------------------|-------------------------------|
| Mini 14' - 34'   | see price list for 6 lengths  |
| Miser 14' - 240' | see price list for 27 lengths |
| Retro 40' - 150' | see price list for 12 lengths |

### IN-PIPE 240 V

| Description       | Catalog #                   |
|-------------------|-----------------------------|
| Retro 160' - 250' | see price list for 10 sizes |

## RAYCHEM FREEZGARD

- Crankcase heaters ➡



### FREEZGARD 120 V

| Description  | Catalog # |
|--------------|-----------|
| 120 V Heater | CCH-1C    |

### FREEZGARD 240 V

| Description  | Catalog # |
|--------------|-----------|
| 240 V Heater | CCH-2C    |

### North America

Tel: +1.800.545.6258  
Fax: +1.800.527.5703  
thermal.info@nVent.com

### Latin America

Tel: +1.713.868.4800  
Fax: +1.713.868.2333  
thermal.info@nVent.com



Our powerful portfolio of brands:

nVent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

© 2018 nVent. Raychem-LC-H59480-ResidentialCableCardCND-EN 18/06