



NVENT CADDY SPEED LINK LD WITH HOOK



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

SPECIFICATIONS

- Wire Rope Diameter:** 1.5 mm
- Static Load Safety Factor:** 5:1
- Material:** Stainless Steel 304 (EN 1.4301)

Catalog Number	Item Name	Wire Rope Length	A	B	C	Static Load(F)	Packing Quantity
SLD15L10S	195945	10 m	58.40 mm	22.9 mm	6.4 mm	195 N	1.0000
SLD15L2S	195935	2 m	58.40 mm	22.9 mm	6.4 mm	195 N	1.0000
SLD15L5S	195940	5 m	58.40 mm	22.9 mm	6.4 mm	195 N	1.0000


Width(W): 12.700 mm

Height(H): 19 mm

ADDITIONAL PRODUCT DETAILS

Wire and pre-assembled hook end fitting made of Stainless Steel 316 (1.4401).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER