



NVENT CADDY SPEED LINK SLK LOCKING DEVICE



CERTIFICATIONS



FEATURES

- Push/pull keyless release allows easy adjustments
- Low-profile locking device minimizes visual impact
- Cable spread of 90 degrees allows positioning the device closer to the load
- Keyless release tubes are easy to operate while wearing gloves
- Double-sided locking mechanism enables simple height adjustment

SPECIFICATIONS


Material: Steel;Polypropylene;Zinc Alloy

Catalog Number	Item Name	Wire Rope Diameter	Height(H)	Width(W)	Thickness(T)	Angle(a)	Packing Quantity	Certifications
SLK2C200	196600	1.5 – 2.0 mm	55 mm	19 mm	12.50 mm	90° Max	1.0000	cUL, ITB, UL
SLK3C200	196730	3 mm	62 mm	24 mm	16 mm	90° Max	1.0000	

ADDITIONAL PRODUCT DETAILS

Locking devices are only to be used with nVent CADDY Speed Link wire spools and accessories with the same specified Wire Rope Diameter as the locking device. Do not use with any other wires.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER