

CRIMPING COMPRESSION TOOL DIE, TYPE M2



FEATURES

Suitable for cable lugs and connectors

SPECIFICATIONS

Catalog Number	Item Name	Lug/Connector Type	Conductor Size	Crimping Width	Tool
PKM2120	716949	Heavy-Duty DIN46235	120 mm ² Stranded, 250 kcmil Stranded	5 mm	M2H, M2M
PKM2150	716950	Heavy-Duty DIN46235	150 mm ² Stranded, 300 kcmil Stranded	5 mm	M2H, M2M
PKM216	716943	Heavy-Duty DIN46235	#6 Stranded, 16 mm ² Stranded	5 mm	M2H, M2M
PKM2185	716951	Heavy-Duty DIN46235	185 mm ² Stranded, 350 kcmil Stranded	5 mm	M2H, M2M
PKM2240	716952	Heavy-Duty DIN46235	240 mm ² Stranded, 500 kcmil Stranded	5 mm	M2H, M2M
PKM225	716944	Heavy-Duty DIN46235	#3 Stranded, 25 mm ² Stranded	5 mm	M2H, M2M
PKM2300	716953	Heavy-Duty DIN46235	300 mm ² Stranded, 600 kcmil Stranded	5 mm	M2H, M2M
PKM235	716945	Heavy-Duty DIN46235	#2 Stranded, 35 mm ² Stranded	5 mm	M2H, M2M
PKM250	716946	Heavy-Duty DIN46235	1/0 Stranded, 50 mm ² Stranded	5 mm	M2H, M2M
PKM270	716947	Heavy-Duty DIN46235	2/0 Stranded, 70 mm ² Stranded	5 mm	M2H, M2M
PKM295	716948	Heavy-Duty DIN46235	4/0 Stranded, 95 mm ² Stranded	5 mm	M2H, M2M
RKM210	716931	Standard	#7 Stranded, 10 mm ² Stranded	5 mm	M2H, M2M

Catalog Number	Item Name	Lug/Connector Type	Conductor Size	Crimping Width	Tool
RKM2120	716938	Standard	120 mm ² Stranded, 250 kcmil Stranded	5 mm	M2H, M2M
RKM2150	716939	Standard	150 mm ² Stranded, 300 kcmil Stranded	5 mm	M2H, M2M
RKM216	716932	Standard	#6 Stranded, 16 mm ² Stranded	5 mm	M2H, M2M
RKM2185	716940	Standard	185 mm ² Stranded, 350 kcmil Stranded	5 mm	M2H, M2M
RKM2240	716941	Standard	240 mm ² Stranded, 500 kcmil Stranded	5 mm	M2H, M2M
RKM225	716933	Standard	#3 Stranded, 25 mm ² Stranded	5 mm	M2H, M2M
RKM2300	716942	Standard	300 mm ² Stranded, 600 kcmil Stranded	5 mm	M2H, M2M
RKM235	716934	Standard	#2 Stranded, 35 mm ² Stranded	5 mm	M2H, M2M
RKM250	716935	Standard	1/0 Stranded, 50 mm ² Stranded	5 mm	M2H, M2M
RKM26	716930	Standard	#10 Stranded, 6 mm ² Stranded	5 mm	M2H, M2M
RKM270	716936	Standard	2/0 Stranded, 70 mm ² Stranded	5 mm	M2H, M2M
RKM295	716937	Standard	4/0 Stranded, 95 mm ² Stranded	5 mm	M2H, M2M

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER