

NVENT ERIFLEX SPIRFLEX SPIRAL SLEEVE



CERTIFICATIONS



FEATURES

Expandable cabling sleeves for many applications

Spiral structure allow cables to branch out at any point

Flexible bundling and mechanical protection of electrical cables and wires

Packed in easy dispense boxes

Halogen free

SPECIFICATIONS

Material: Polyethylene

Flammability Rating: UL® 94HB

Working Temperature: -50 to 85 °C

Catalog Number	Item Name	Color	Diameter	Length	Unit Weight
SPIRFLEX-I6	556000	Black	6 mm	50 m	0.012 kg
SPIRFLEX-X6	556100	White	6 mm	50 m	0.012 kg
SPIRFLEX-I12	556010	Black	12 mm	25 m	0.034 kg
SPIRFLEX-X12	556110	White	12 mm	25 m	0.034 kg
SPIRFLEX-I16	556020	Black	16 mm	25 m	0.046 kg
SPIRFLEX-I22	556030	Black	22 mm	25 m	0.060 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER