


# EARTHING AND NEUTRAL BUSBAR WITH GREEN/YELLOW DIN RAIL CLIP



Earthing and Neutral Busbars with Green/Yellow DIN Rail Clips are used to connect multiple earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, wind and solar power generation and in data centers.

## CERTIFICATIONS



## FEATURES

Use to connect several earthing conductors

Easy for the installer to add connections

Chamfered holes allow for easy connections

Rigid bar

Quick and easy installation on DIN rail

Halogen free

RoHS compliant


## SPECIFICATIONS

**Material:** Brass;Polyethylene

Product Attribute	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 7 Connections	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 12 Connections	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 15 Connections
Catalog Number	EB7GYSUP	EB12GYSUP	EB15GYSUP
Item Name	568678	568679	568680
Number of Connections	7	12	15
Conductor Size, IEC	(1) 6 - 25 mm <sup>2</sup> Stranded (6) 1.5 - 16 mm <sup>2</sup> Stranded	(1) 6 - 25 mm <sup>2</sup> Stranded (11) 1.5 - 16 mm <sup>2</sup> Stranded	(1) 6 - 25 mm <sup>2</sup> Stranded (14) 1.5 - 16 mm <sup>2</sup> Stranded

Product Attribute	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 7 Connections	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 12 Connections	Earthing & Neutral Busbar, Brass on Yellow/Green DIN Rail Clip, 15 Connections
Max Current Rating	40 A	40 A	40 A
Cross Section	63 mm <sup>2</sup>	63 mm <sup>2</sup>	63 mm <sup>2</sup>
Depth(D)	7 mm	7 mm	7 mm
Width(W)	57 mm	92 mm	113 mm
Height(H)	9 mm	9 mm	9 mm
Thread Size(TS)	M5	M5	M5
Hole Size 1(HS1)	6.5 mm	6.5 mm	6.5 mm
Hole Size 2(HS2)	5.5 mm	5.5 mm	5.5 mm
Torque(TQ)	2 N-m	2 N-m	2 N-m
Unit Weight	0.030 kg	0.047 kg	0.057 kg
Complies With	IEC® 60998-2-1	IEC® 60998-2-1	IEC® 60998-2-1

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**