

PDRG PERFORATED ASYMMETRIC PROFILE



FEATURES


- Rapid assembly of all kinds of frameworks
- High mechanical resistance
- High corrosion resistance
- Conforms to EN 60715 and 50035 and DIN 46277
- RoHS compliant

SPECIFICATIONS

- Finish** Electrogalvanized
- Material** Steel

Catalog Number	Item Name	Height(H)	Width(W)	Length(L)	Thickness(T)	A	B	C	D	Unit Weight
PDRG-2M	558050	32 mm	15 mm	2,000 mm	1.50 mm	9 mm	7 mm	18 mm	6.2 mm	1.300 kg
PDRG-3M	558060	32 mm	15 mm	3,000 mm	1.50 mm	9 mm	7 mm	18 mm	6.2 mm	1.960 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.