

310 Beam Clamps


Part Description	Part Number	A (mm)	B (mm)	М	Ø	T (N*m)	*F (N)	Pipe Size (Nominal)	Approval
310M10	389890	33	54.5	М10	M10	7	2500	> 2" \le 4"	VdS &c FM
31011MM	598501	33	54.5	M10	11mm	7	2500	> 2" \le 4"	VdS &c FM
310M12	388890	33	62	M12	M12	14	3500	> 4" ≤ 6"	VdS &c FM
31013MM	598502	33	62	M12	13mm	14	3500	> 4" < 6"	∀dS &c FM

VdS Approval Number G4080038

F = Maximum allowable static load (N)







- 1. ERICO products shall be installed and used only as indicated in ERICO product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative.
- 2. ERICO products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
- 3. All instructions must be completely followed to ensure proper and safe installation and performance.
- 4. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.
- 5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment
- 6. All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads unless otherwise noted.

The Customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

IS51\_B

FM is a registered certification mark of FM Approvals LLC, LTD UL is a registered trademark of UL LLC.

VdS is a registered trademark of VdS Schadenverhutung GmbH

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are registered trademarks of ERICO International Corporation.

TECHNICAL SUPPORT:

www.erico.com

1 of 1



