

NVENT ERIFLEX FLEXIBAR ADVANCED KIT



CERTIFICATIONS



FEATURES

Connects busbar to fixed switchgear

Kit includes preformed nVent ERIFLEX Flexibar Advanced with punched ends and end covers

Kit can be used in three configurations

Insulated by high-resistance, halogen free, flame retardant and low smoke material with less than 20% contact with conductor for high flexibility

Tinned copper allows for copper or aluminum conductor connections

RoHS compliant

SPECIFICATIONS

Halogen Free Rating:	UL® 2885;IEC® 60754-1;IEC® 62821-1
Smoke, Toxicity and Acidity Rating:	IEC® 60754-2
Low Smoke Rating:	IEC® 61034-2;ISO 5659-2;UL® 2885
UV Resistance Rating:	UL® 854;UL® 2556
Flammability Rating:	UL® 94V-0

Catalog Number	Item Name	Typical Application Current Rating	Type	Unit Weight
FLXADVKIT250AT	534800	250 A	Three Phase	0.760 kg
FLXADVKIT250ATN	534805	250 A	Three Phase with Neutral	0.980 kg

Catalog Number	Item Name	Typical Application Current Rating	Type	Unit Weight
FLXADVKIT630AT	534810	630 A	Three Phase	2.100 kg
FLXADVKIT630ATN	534815	630 A	Three Phase with Neutral	3.100 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER