



EER TRAPEZOIDAL DECK HANGER



CERTIFICATIONS



FEATURES

Supports wire from decking


SPECIFICATIONS

Catalog Number	Item Name	Material	Finish	Flange Thickness(FT)	Hole Size(HS)	Drill Bit Diameter	Static Load 1(F1)	Static Load 2(F2)	Packing Quantity
EER	171470	Spring Steel	nVent CADDY Armour	0.8 – 3.0 mm	6.80 mm	7 mm	450 N	900 N	1.0000

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER