





BC-MSM CONDUIT TO BEAM CLAMP, SIDE MOUNT



CERTIFICATIONS



FEATURES


- Easy installation to beam flanges
- Eliminates offset bending conduit
- Conduit clip rotates 360 degrees

SPECIFICATIONS

Finish nVent CADDY Armour
Material Spring Steel

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter(OD)	Torque(TQ)	Static Load(F)
BC812MSM	1/2", 3/4"	1/2", 3/4"	0.709" – 1.181"	20 ft lb	25 lb
BC16MSM	3/4", 1"	3/4", 1"		20 ft lb	25 lb
BC20MSM	1 1/4"	1 1/4"		20 ft lb	25 lb
BC24MSM	1 1/2"	1 1/2"		20 ft lb	25 lb
BC32MSM	2"	2"		20 ft lb	25 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.