



CD-TDH CONDUIT/PIPE TO DECK HANGER



FEATURES

Meets the requirements of NEC® Section 300.4(E)

Supports conduit or pipe 1-1/2" (38 mm) under the roof decking to prevent potential damage from nails or screws

SPECIFICATIONS

Finish Electrogalvanized

Material Steel

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Roof Decking Sheet Thickness	Trapeze Width
CD0BTDH	1/2"	1/2"	24 GA Min	2" Max
CD1BTDH	3/4"	3/4"	24 GA Min	2" Max
CD2BTDH	1"	1"	24 GA Min	2" Max
CD2.5BTDH	1 1/4"		24 GA Min	2" Max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.