



115FL STANDARD DUTY LOOP HANGER, FELT LINED, 2" PIPE, 2.375" OD, 3/8" ROD

CATALOG NUMBER

1150200FL



CERTIFICATIONS



FEATURES

Flared edges help prevent sharp surfaces from coming into contact with the pipe

Recommended for the suspension of stationary non-insulated copper tubing lines to prevent electrolysis

Felt lining also acts to reduce noise in pipes

Retained insert nut helps ensure the loop hanger and insert nut stay together

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Pipe Size: 2"

Outer Diameter: 2 3/8"

Rod Size: 3/8"


A: 4 1/4"

B: 1 13/16"

C: 7/8"

Static Load: 300 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.