




NVENT CADDY FLAT RIGID BOX SUPPORT BRACKET BETWEEN STUD ASSEMBLY



FEATURES

Stamped with A- and B-side markings that allow mounting for all box types and configurations – no need for removal of screws – simply flip and it's ready to use

Bracket is completely flat, no offset

Floor stand positions boxes 18 1/2" from the floor for consistent placement

SPECIFICATIONS

Knockout Sizes, Box 2	(12) 1/2", 3/4"
Knockout Sizes, Box 1	(4) 1/2", 3/4";(8) 1/2"
Finish	Pregalvanized
Material	Steel

Catalog Number	Volume, Box 1	Stud Spacing	Position, Box 2	Position, Box 1	Mud Ring Type	Ground Wire Included, Box 2	Ground Wire Included, Box 1	Gang, Box 2	Gang, Box 1	Drywall Thickness	Box Size 2	Box Size 1	Box Depth	Volume, Box 2
F3A4DM10P1M5	30.3 in ³	8" – 16"	Right	Left	Raised	Yes	Yes	1	1	3/4"	4 11/16"	4"	2 1/8"	42 in ³
F3A4D0P1	30.3 in ³	8" – 16"	Right	Left		Yes	Yes				4 11/16"	4"	2 1/8"	42 in ³

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.