




# ROL14 STRUT MOUNTED ROLLER



## FEATURES


Designed for strut mounting

For applications where there is longitudinal pipe movement

## SPECIFICATIONS

Catalog Number	Material	Finish	Pipe Size
ROL14000EG	Steel	Electrogalvanized	6" – 16"

## DIAGRAMS



Pipe Size	Saddle Number	Covering Thickness	Outer Diameter	Radius	A	B
6"	None	0"	6 5/8"	3 5/16"	9 9/16"	6 7/8"
	630	1"	9"	4 1/8"	10 3/16"	7 7/8"

631	1 1/2"	10"	5"	10 5/8"	8 3/8"	
632	2"	11"	5 1/2"	11"	8 7/8"	
633	2 1/2"	12"	6"	11 3/8"	9 3/8"	
634	3"	13"	6 1/2"	11 3/4"	9 7/8"	
635	4 1/8"	15 1/4"	7 5/8"	12 1/2"	10 15/16"	
8"	None	0"	8 5/8"	4 5/16"	10 1/4"	7 13/16"
	631	1 1/2"	12"	6"	11 3/8"	9 3/8"
	632	2"	13"	6 1/2"	11 3/4"	9 7/8"
	633	2 11/16"	14 3/8"	7 3/16"	12 3/16"	10 7/16"
	634	3 1/8"	15 1/4"	7 5/8"	12 1/2"	10 15/16"
	635	4 1/8"	17 1/4"	8 5/8"	13 1/4"	11 7/8"
10"	None	0"	10 3/4"	5 3/8"	11"	8 13/16"
	631	1 1/2"	14 1/4"	7 1/8"	12 1/8"	10 7/16"
	632	2 1/16"	15 1/4"	7 5/8"	12 1/2"	10 15/16"
	633	2 9/16"	16 1/4"	8 1/8"	12 13/16"	11 3/8"
	634	3 1/16"	17 1/4"	8 5/8"	13 1/8"	11 7/8"
	635	4 1/16"	19 1/4"	9 3/4"	13 7/8"	12 13/16"
12"	None	0"	12 3/4"	6 3/8"	11 11/16"	9 3/4"

631	1 9/16"	16 1/8"	8 1/16"	12 7/8"	11 3/8"	
632	2 1/16"	17 1/4"	8 5/8"	13 1/4"	11 7/8"	
633	2 5/8"	18 1/4"	9 1/8"	13 9/16"	12 5/16"	
634	3 1/16"	19 1/4"	9 5/8"	13 7/8"	12 13/16"	
635	4 1/8"	21 3/8"	10 11/16"	14 5/8"	13 3/4"	
14"	None	0"	14"	7"	12 1/16"	10 5/16"
	631	1 1/2"	17 1/2"	8 3/4"	13 3/16"	11 7/8"
	632	2"	18 3/8"	9 3/16"	13 9/16"	12 5/16"
	633	2 1/2"	19 3/8"	9 11/16"	13 7/8"	12 13/16"
	634	3"	20-3/8"	10 3/16"	14 1/4"	13 1/4"
	635	4"	22 3/8"	11 3/16"	14 7/8"	14 1/4"
16"	None	0"	16"	8"	12 3/4"	11 5/16"
	631	1 1/2"	19 5/8"	9 13/16"	13 7/8"	12 13/16"
	632	2"	20-3/8"	10 3/16"	14 13/16"	13 1/4"
	633	2 1/2"	21 5/8"	10 13/16"	14 1/2"	13 3/4"
	634	3"	22 1/8"	11 1/16"	14 7/8"	14 1/4"
	635	4"	24 3/8"	12 3/16"	15 1/2"	15 1/8"

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.