


EARTHBRIDGE B162, TWO STUD, CABLE TO SOLID ROUND STEEL



DIAGRAMS



FEATURES

Long-lasting design

Low ground resistance and impedance

Superior electrical conductivity and resistance to corrosion

Electrically and mechanically robust and reliable

Easy to install

SPECIFICATIONS


| Catalog Number | Material | Earth Joint Type | Conductor Type | Conductor Size | Length 2 (L2) | Length 1 (L1) | Depth (D) | Width 1 (W1) | Width 2 (W2) | Diameter (Ø) | Thread Size (TS) | Angle (a) |
|----------------|---------------|------------------|--|-----------------------------|---------------|---------------|-----------|--------------|--------------|--------------|------------------|-----------|
| B1622QC701 | Copper, Steel | B162, Two Stud | Yellow-Green Insulated Cable to Solid Round Steel, 10° Angle | 70 mm ² Stranded | 4" | 39.370" | 1 5/8" | 1 3/4" | 3 1/4" | 0.470" | 1/2" UNC | 10° |

ADDITIONAL PRODUCT DETAILS

Earthbridges are assemblies made from a high-quality conductive earthpoint (connecting terminal) and various types of conductors. The nVent ERICO Cadweld exothermic connection process is used to combine them together, forming a highly corrosion resistant and long-lasting assembly.

Includes (2) brass bolts and (2) brass washers.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm.- For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.