

PREFABRICATED FENCE CLAMP ASSEMBLY WITH SINGLE GROUND LEAD, LEFT HAND, 2" FENCE POST, 4/0 STRANDED, 4' GROUND

CATALOG NUMBER

A235D2Q4LH



FEATURES

Ideal for when nVent ERICO Cadweld connections cannot be made to aluminum pipe or thin-wall steel tube

Stainless steel hardware included

Available in either left or right-hand orientation

PRODUCT ATTRIBUTES

Material: Copper;Stainless Steel 18-8 (EN 1.4305);Stainless Steel 304 (EN 1.4301)

Finish: Tinned

Orientation: Left Hand

Fence Post Size, Nominal: 2"

Fence Post Outside Diameter, Actual: 2.38"


Ground Lead Conductor Size: 4/0 Stranded

Ground Lead Length: 4'

ADDITIONAL PRODUCT DETAILS

Right hand orientation shown in diagram.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.