


# PLUG BOND MULTIPURPOSE KIT, SIGNAL



## FEATURES

Used when a standard plug bond cannot be installed from the field side of a rail in tight areas such as frogs and switches

Highly flexible cable is resistant to vibration fatigue

Insulation manufactured from 600 volt-rated PVC

Insulation thickness available: 4/64" (0.063", 1.6 mm)

## SPECIFICATIONS

**Number of Wires** 133  
**Conductor Type** AREMA® S-8

Catalog Number	Material	Insulated	Color	Conductor Size	Insulation Thickness	Length(L )
SBPMJR12	Cadmium Bronze, Polyvinylchloride	Yes	Black	3/16" Bondstrand	1/16"	12"
SBPMJS12	Cadmium Bronze, Polyvinylchloride	Yes	Orange	3/16" Bondstrand	0.063"	12"
SBPMJS14	Cadmium Bronze, Polyvinylchloride	Yes	Orange	3/16" Bondstrand	0.063"	14"
SBPMJ310	Cadmium Bronze	No		3/16" Bondstrand		10"
SBPMJ312	Cadmium Bronze	No		3/16" Bondstrand		12"
SBPMJ314	Cadmium Bronze	No		3/16" Bondstrand		14"

## ADDITIONAL PRODUCT DETAILS

---

Kit includes: (1) tube of plug bond grease, (2) plug bond track connectors, signal, 15' (0.3 m) of orange Insulated 3/16" bondstrand, (2) tinned copper compression sleeves, (4) wooden tie conductor fixing staples, (2) hammer-on rail clips, one conductor perpendicular to foot, (2) 9" (229 mm) long heat shrink tubing, and (2) 18" (457 mm) long polyethylene bootleg riser with hole.

Plug Bond Grease (T369) recommended when installing.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.