

## BD CRIMP AND DRILL TOOL



### CERTIFICATIONS



### FEATURES

For crimping and drilling of braid terminals

Use with FRCB Flat Braid in Coil, Plain Copper and FTGB Flat Braid in Coil, Tinned Copper

Includes guide and drill bit

### SPECIFICATIONS

Catalog Number	Item Name	Cross Section	Drill Bit Diameter	Screw Diameter	Unit Weight
BD16	558610	31.570 kcmil	6.5 mm	M6	1.440 lb
BD16-8	558640	31.570 kcmil	8.5 mm	M8	1.440 lb
BD25	558620	49.300 kcmil	11 mm	M10	1.490 lb
BD50	558630	98.680 kcmil	12.5 mm	M12	1.570 lb

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.