

EJECTION STOP KIT



CERTIFICATIONS



FEATURES

Holds nVent ERIFLEX Flexibar laminates in place while punch is raised

Pressure plates notched to apply pressure to laminates without damaging the insulation

Punch tip remains visible when kit is attached to puncher

RoHS compliant

SPECIFICATIONS

Catalog Number	Item Name	Product	Material	Punch Size	Unit Weight
EJECSTOP18-20S	545896	Replacement Ejection Stop	Elastomere	18.0 mm, 20.0 mm	0.130 lb
EJECSTOP6-14S	545895	Replacement Ejection Stop	Elastomere	6.5 mm, 9.0 mm, 11.0 mm, 14.0 mm, 5/16", 3/8", 17/32", 9/16"	0.150 lb
EJECSTOP18-20L	545894	Ejection Stop with Pressure Plates	Steel, Elastomere	18.0 mm, 20.0 mm	0.620 lb
EJECSTOP6-14L	545893	Ejection Stop with Pressure Plates and Washer	Steel, Elastomere	6.5 mm, 9.0 mm, 11.0 mm, 14.0 mm, 5/16", 3/8", 17/32", 9/16"	1.210 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.