

SAVE TIME.
SAVE MONEY.
SAVE SPACE.
SAVE LIVES.

PYROTENAX

MINERAL INSULATED (M.I.) ELECTRICAL CABLES

BEYOND UL 2196/ULC-S139

nVent PRESENTS A PYRO FOR LIFE PRODUCTION A FIRE-RATED CABLE FILM "BETTER THAN CONCRETE" SYSTEM 1850
CIRCUIT CONDUCTING COPPER CONDUCTORS INSULATION FIRE MAGNESIUM OXIDE AND SEAMLESS COPPER SHEATH
CLASSIFICATION TESTING UL 2196/ULC-S139 INSULATION VOLTAGE RATING 600V CONDUCTOR SIZE 16 AWG - 500 KCMIL MAXIMUM EXPOSURE 1850°F (1010°C)

2

RATED 2 HOURS

FIRE-RESISTIVE CABLE TESTED TO THE
UL 2196/ULC-S139 FIRE TEST STANDARDS

NO SMOKE

go.nVent.com/NoSmoke

nVent
PYROTENAX