

MOISTURE PROTECTION KIT FOR STRAIGHT THROUGH JOINT

nVent PYROTENAX STJMPRO is a range of kits that offer moisture protection for field installed, non fire-rated splices of nVent PYROTENAX mineral insulated (MI) cable.



FEATURES

Simple and fast to install: heat shrinkable polymer kit

Wide range of sizes

Suitable for all single and multiconductor cables

Temperature rating: 90 °C / 194 °F

SPECIFICATIONS

| Catalog Number | Item Name |
|----------------|---------------------------|
| STJMPRO114A | STJ MOIST PROT KIT 1-1/4" |
| STJMPRO12A | STJ MOIST PROT KIT 1/2" |
| STJMPRO12B | STJ MOIST PROT KIT 1/2" |
| STJMPRO12C | STJ MOIST PROT KIT 1/2" |
| STJMPRO1A | STJ MOIST PROT KIT 1" |
| STJMPRO34A | STJ MOIST PROT KIT 3/4" |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER