

33500

NH switch disconnecter with fuses



Connection	box terminal
W	106
H	200
Rated current	125 A
Size	NH 00

Description: 3-pole NH switch disconnecter with fuses. With multifunction handle (snap action switch mechanism). Connection at the bottom.

Rated voltage: 690 V

For busbars: 12, 15, 20, 25, 30 × 5, 10

Power dissipation at 80% load: 18.6 W(33500), 52.5 W (33510)

Pack quantity: 1 pc.

Approvals: IEC, VDE, DNV GL

Snap -action switch enables safe operator-independent switching.