

# ADIS05040

Inner doors



## Inner doors, 400 pre-grained stainless steel

H	500
W	400
N° of locks	1
Item no.	ADIS05040
h - Inner door dimensions	445
w - Inner door dimensions	292

**Description:** For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening (Machining is required). Double-bit 3 mm lock, 800 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm, adjustable depth position with AMG accessory. Workable area: H-55, W-108. 19" version available on request.

**Material:** Door 1.5 mm AISI 304 stainless steel and vertical top and bottom profiles 2 mm, AISI 304 stainless steel.

**Protection:** IP 2XC.

**Finish:** 400 pre-grained stainless steel.

**Pack quantity:** Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

Displays and indicators can be mounted, on a surface within the enclosure while covering other components, and preventing unauthorized access.