

BP4608SS

Vortex cooler



This Vortex cooler, BP, with a IP 66 protection degree, is easy to install, has no moving parts, and is maintenance free. In addition to cooling, it also reduces the relative humidity within the enclosure it is mounted on. This Vortex cooler is an ideal solution to prevent overheating within the enclosure.



IP 66 | TYPE 4X

IP 66 | TYPE 4X, Stainless steel

Low pressure relief valve	Yes
Silencer included	No
H	126
Air flow (l/min)	227
Noise (dB)	78
Cooling Capacity (W)	162
Installation cut-out diam. (mm)	33
Air inlet	1/8"
Weight (kg)	0.35
Item no.	BP4608SS

Description: Compact, reliable and low cost way to cool and purge enclosures. It produces cold air from compressed air, with no moving parts. The easy mounting through a standard electrical knockout makes this solution especially suitable to be installed even when the enclosures are already in the field. For a continuous Vortex operating, relative humidity inside the enclosure is maintained below 45%, no moisture condenses inside the enclosure (the enclosure must be sealed). Most TYPE 4 and 4X units include a silencer to minimize the noise. The coolers must be installed vertically to maintain the protection degree.

Material: Internal Vortex tube manufactured in stainless steel. External cover, BP TYPE 12 in plastic and aluminium, BP TYPE 4 in aluminium, and 4X in stainless steel.

Protection: Depending on type, up to IP66 | TYPE 4X.

Pack quantity: Vortex cooler with mounting accessories.