



Description: Brass solenoid valve and thermostat that limit the flow of compressed air to only when cooling is needed. The thermostat is factory set at 35 °C, but adjustable to any other temperature. The thermostat mounts in a 22 mm diameter hole, and it may be mounted through the enclosure wall or on a bracket inside the enclosure. The thermostatically controlled vortex cooler saves compressed air, and it is recommended where heat load fluctuates and continual purge is not required.

Voltage: 240 V and 50 Hz. Other voltages on request.

Delivery: Thermostat with mounting bracket, and solenoid valve.

For	Item no.
BP/HT 4 × 08; 4 × 15	BPT14
BP/HT 4 × 30; 4 × 40	BPT38