

Brace terminals

Brace terminals



Description: Brace terminal, up to 300mm², for round conductors. Terminal with captive clamping screws, conductor can be overlapped. Indication of nominal cross-section and tightening torque noted on the terminal.

Rated voltage: 690 V

Approvals: UL

For use up to max.	Connection min-max	For busbar	Pack quantity	Item no.
480 A	35 - 150 mm ² , lam. Cu. 15 × 5 ... 20 × 10	12, 15, 20 × 5, 10	6 pcs.	01135
500 A	Cu / Al 95 - 185 mm ²	20, 25, 30 × 5, 10	6 pcs.	01318
600 A	Cu / Al 95 - 300 mm ²	20, 25, 30 × 5, 10	3 pcs.	01760