

# CAG20

Cable anchorage glands | Power Distribution



H	17-20
H2	5.7
Metric	M20
Diameter	34-37
Cable diameter (mm)	7-11
Hole diameter (mm)	20.5
Item no.	CAG20

**Description:** Two-component grommet with membrane seal and cable anchorage. The installation does not require tools, it is self-adjusting to its surrounding wall thickness and click-fixed in place. Because of its compact design it only extends 5.7 mm outside the enclosure on which it is mounted. The “pushout” membrane is a permanent seal until it is penetrated by a cable or pipe. Suitable for holes in materials of 0.7 to 3 mm thickness.

**Material:** TPE and polyamide 66, halogen free.

**Temperature resistance:** -20 °C to +125 °C.

**Finish:** RAL 7035.

**Protection:** IP 67, 65, waterproof.

**Pack quantity:** 50 pieces.

This two component cable gland can be mounted on a wide range of enclosures. It secures the cable into position, and eliminates any external strains.