

CED16

Double protection cables entry | Power Distribution



H	17.7
H1	11.0
Metric	M16
Diameter	21.0
Cable diameter (mm)	5-9
Hole diameter (mm)	16.5
Pack quantity	50
Item no.	CED16

Description: The rubber grommet is very simple to use. The installation does not require tools, which in turn means lower work cost. The "pushout" membrane is a permanent seal until it is penetrated by a cable or pipe. Suitable for holes in materials of 0.5 to 4 mm thickness.

Material: EPDM, halogen free.

Temperature resistance: -40 °C to +110 °C.

Finish: RAL 7035.

Protection: IP 67.

The rubber cable gland is easy to mount, and, cables and pipes can be pulled through easily without tools, ensuring that the enclosure's protection degree is maintained.