

# CED40

Double protection cables entry | Power Distribution



H	29.5
H1	21.7
Metric	M40
Diameter	48.5
Cable diameter (mm)	19-28
Hole diameter (mm)	40.5
Pack quantity	25
Item no.	CED40

**Description:** The rubber grommet is very simple to use. The installation does not require tools, which in turn means lower work cost. The "pushout" membrane is a permanent seal until it is penetrated by a cable or pipe. Suitable for holes in materials of 0.5 to 4 mm thickness.

**Material:** EPDM, halogen free.

**Temperature resistance:** -40 °C to +110 °C.

**Finish:** RAL 7035.

**Protection:** IP 67.

The rubber cable gland is easy to mount, and, cables and pipes can be pulled through easily without tools, ensuring that the enclosure's protection degree is maintained.