

# CLPF-IEC\_CN

Mounting profiles | Floor Standing Enclosures



HOFFMAN

CONNECT AND PROTECT



**Description:** The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nut, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

**Material:** Zinc plated steel.

**Pack quantity:** 4 profiles including snap-line for fixing.

H/W	W/D	Max. loading Horizontal C	Max. loading Horizontal	Item no.
400	400	800 N	1000 N	CLPF400
500	500	800 N	1000 N	CLPF500
600	600	800 N	1000 N	CLPF600
800	800	800 N	1000 N	CLPF800
	1000	800 N	1000 N	CLPF1000
	1200	800 N	1000 N	CLPF1200
	1400	Only vertical loads allowed	Only vertical loads allowed	CLPF1400
	1600	Only vertical loads allowed	Only vertical loads allowed	CLPF1600
	1800	Only vertical loads allowed	Only vertical loads allowed	CLPF1800
	2000	Only vertical loads allowed	Only vertical loads allowed	CLPF2000
	2200	Only vertical loads allowed	Only vertical loads allowed	CLPF2200