

Connection busbar support

Connection busbar support



Description: Connection busbar support with integrated terminals (1,5 - 16 mm²) for feeding or tapping the busbar with internal scw holes. May also be used as centre support.

Rated voltage: 690 V

Rated current: 63 A

Rated frequency: 50/60 Hz

Rated isolation voltage Ui: 1000 V

Rated surge voltage Uimp: 6 kV

Short circuit withstand: 14 kA (max 400 mm distance between supports)

Power dissipation 80% of rated current: 0.5 W

Dimensions: 20 × 202 × 87 mm

Pack quantity: 10 pcs.

Approvals:

N° of Poles	For busbar	Item no.
3	12, 20, 30 × 5, 10	01484