

# Connection terminal plate

Connection terminal plate



**Description:** Connection terminal plate, 3-pole, with cover cap.

**For busbars:** 12, 15, 20, 25, 30 × 5, 10.

**Rated voltage:** 690 V

**Rated peak withstand current Ipk max:** 40.5 kA (01240), 56.3 kA (01243)

**Pack quantity:** 1 pc.

**Approvals:** CSA, UL, GL

Width	For use up to max.	Connection	Item no.
54	300 A	6 - 50 mm <sup>2</sup> , lam. Cu. 7 × 4 ... 9 × 10	01240
81	440 A	35 - 120 mm <sup>2</sup> , lam. Cu. 12 × 4 ... 15.5 × 10	01243