



ERICO

NVENT ERICO CADWELD FLYAWAY PROGRAM

SPECIAL HANDLING AND EXPEDITED SERVICE PROGRAM FOR CADWELD PRODUCTS*

PRODUCTS:

STOCKED MOLDS & ASSOCIATED ITEMS

- See reference list of stocked parts and associated quantities
- Same day shipments based on order receipt timing

NON-STOCKED MOLDS

- Molds previously designed and active
- Next business day shipment for most non-stocked molds based on order receipt timing

ACCESSORIES

- Required handle clamps, frames, welding material and accessories to install a connection

TIMING:

STOCKED ITEMS

- Orders received by 12:30 PM EST will be shipped the same day

NON-STOCKED ITEMS

- Orders received by 12:30 PM EST will be shipped the next business day
- Some non-stocked molds (Price Keys G, K, L, S, V) may take two business days

Add one day to all orders received after 12:30 PM EST. Maximum allowable quantity of molds per order is 10. Minimum quantities are also noted on some stocked accessories.

TERMS AND CONDITIONS:

TERMS AND CONDITIONS

- Standard nVent "Terms and Conditions of Sale" apply
- Minimum billing is waived
- Customer must specify method of shipment
- All Flyaway freight charges are pre-pay and add

ON STOCKED ITEMS

- Standard nVent "Terms and Conditions of Sale" apply

ON NON-STOCKED ITEMS

- Premium Flyaway pricing and distributor discounts apply
- Returns are not allowed

NOTES:

- All orders must be sent through your local Cadweld representative.
- nVent ERICO specialty items, such as custom designed signal reference grid, ground mats and mesh, etc., do not apply to this service.
- For orders with both stocked and non-stocked items, combined order will ship complete based on the non-stocked items.

*Cadweld products included in this program are noted on reference list.

Product Number	Min/Max Order Qty
----------------	-------------------

Welding Material	Min/ Max
------------------	----------

15	20/200
25	20/200
32	20/200
45	20/200
65	20/200
90	10/200
115	10/200
150	10/200
200	10/200
250	10/200
500	10/200
15PLUSF20	20/200
25PLUSF20	20/200
32PLUSF20	20/200
45PLUSF20	20/200
65PLUSF20	20/200
90PLUSF20	10/200
115PLUSF20	10/200
150PLUSF20	10/200
200PLUSF20	10/200
250PLUSF20	10/200
300PLUSF20	10/200
400PLUSF20	10/200
500PLUSF20	10/200
CA15	20/200
CA25	20/200
CA32	20/200
CA45	20/200
CA15PLUSF33	20/200
CA25PLUSF33	20/200
CA32PLUSF33	20/200
CA45PLUSF33	20/200
CA25XF19	20/40
CA32XF19	20/40
CA45XF19	20/40
CA25PLUSXF19	20/40
CA32PLUSXF19	20/40
CA45PLUSXF19	20/40
XL25	12/40
XL32	12/40
XL45	12/40
XL90	12/40
XL115	12/40
XL150	12/40

Cadweld Plus	One Shots	Min/Max
--------------	-----------	---------

GR1161GPLUS	12/48
GR1141GPLUS	12/48
GR1141LPLUS	12/48
GR1161LPLUS	12/48
GR1162CPLUS	12/48
GR1162GPLUS	12/48
GR1181GPLUS	12/48
GR1181LPLUS	12/48
GR1181VPLUS	12/48
GR1182CPLUS	12/48
GR1182GPLUS	12/48
GR1182QPLUS	12/48
GT1141LPLUS	12/48
GT1161GPLUS	12/48
GT1161LPLUS	12/48
GT1161VPLUS	12/48
GT1162CPLUS	12/48
GT1162GPLUS	12/48
GT1181GPLUS	12/48
GT1181LPLUS	12/48
GT1181VPLUS	12/48
GT1182CPLUS	12/48
GT1182GPLUS	12/48

NT1161GPLUS	12/48
NT1161LPLUS	12/48
NT1161VPLUS	12/48
NT1181GPLUS	12/48
NT1181LPLUS	12/48
NT1181VPLUS	12/48
NX1161GPLUS	12/48
NX1161LPLUS	12/48
NX1161VPLUS	12/48
NX1181VPLUS	12/48

Cadweld One Shots	Min/Max
-------------------	---------

GR1141G	12/48
GR1141L	12/48
GR1161G	12/48
GR1161L	12/48
GR1161V	12/48
GR1162C	12/48
GR1162G	12/48
GR1162Q	12/48
GR1181G	12/48
GR1181L	12/48
GR1181V	12/48
GR1182C	12/48
GR1182G	12/48
GR1182Q	12/48
GT1141G	12/48
GT1141L	12/48
GT1161G	12/48
GT1161L	12/48
GT1161V	12/48
GT1162C	12/48
GT1162G	12/48
GT1181G	12/48
GT1181L	12/48
GT1181V	12/48
GT1182C	12/48
GT1182G	12/48
NT1161G	12/48
NT1161L	12/48
NT1161V	12/48
NT1181G	12/48
NT1181L	12/48
NT1181V	12/48
NX1161G	12/48
NX1161L	12/48
NX1161V	12/48
NX1181V	12/48
PG11L	12/48

Flexible Jumpers	Min/Max
------------------	---------

FJIT24SK	4/20
FJ2G24SK	4/20
FJ2Q24SK	4/20
FJ2G24	4/20
FJ2Q24	4/20

Disks & Battings	Max
------------------	-----

B117A	6 Std Pkgs
B117B	6 Std Pkgs
B117C	6 Std Pkgs
B140A	6 Std Pkgs
B140B	6 Std Pkgs
B141A	6 Std Pkgs
B143A	6 Std Pkgs
B143B	6 Std Pkgs
B144A	6 Std Pkgs
B144B	6 Std Pkgs
B144C	6 Std Pkgs
SCDM01	6 Std Pkg

Sleeves	Max
---------	-----

B112	3 Std Pkgs
B1331H	3 Std Pkgs
B1331K	3 Std Pkgs
B1331L	3 Std Pkgs
B1331V	3 Std Pkgs
B1332C	3 Std Pkgs
B1332Q	3 Std Pkgs
CAB112	3 Std Pkgs

CAB1331H	3 Std Pkgs
CAB1331L	3 Std Pkgs
S01F	3 Std Pkgs
S03F	3 Std Pkgs
S09F	3 Std Pkgs
S20F	3 Std Pkgs

Lugs	Max
------	-----

B101CEOL	2 Std Pkg
B101DEOL	2 Std Pkg
B101EEOL	2 Std Pkg
B101EGOL	2 Std Pkg
B102CEOL	2 Std Pkg
B102EEOL	2 Std Pkg
B102EGOL	2 Std Pkg
B121CE	2 Std Pkg
B121DE	2 Std Pkg
B122CE	2 Std Pkg
B122DE	2 Std Pkg

Tools & Accessories	Max
---------------------	-----

B134	2
B136A	2
B136B	2
B13716	2
B13718	2
KITCDMV01	1
PLUSCU	10
PLUSCULD	10
T111	2
T313	10
T314	5
T320	10
T320A	5
T321	2
T394	10
T403	10
XLB971A1	2
B160V	2
B160VT	2
B396	2
B399A	2
B399B	2
B399ES	2
FMCDMV01	2
L159	10
L160	10
XLL159	10
XLL160	10
Molds	Max
CAHAA1G	10
CAHAA1GA	10
CAHAA1GM	10
CAHAA1H	10
CAHAA1L	10
CAHAA1V	10
CAHAA1VB	10
CAHBA1G	10
CAHBA1G8	2
CAHBA1L	5
CAVST1GA	10
CAVST1GB	2
GLCCE2G	5
GLCDE2G	2
GRC162C	2
GRC162G	2
GRC162Q	10
GRC168C	2
GRC181V	5
GRC182C	5
GRC182G	5
GRC182L	5
GRC182Q	10
GRC188C	2
GRC188D	2
GRC188G	2
GRT181G	5
GRT181H	5
GTC161T	10

GTC161V	10
GTC162C	10
GTC162G	10
GTC162L	5
GTC162Q	10
GTC162QW	2
GTC163Q	2
GTC168C	2
GTC168D	2
GTC168F	2
GTC181T	10
GTC181V	5
GTC182C	10
GTC182G	10
GTC182L	10
GTC182Q	10
GTC182V	5
GTC183Q	10
GTC188C	2
GTC188D	2
GTC188G	2
GTC332Q	2
GTP181G	2
GTP181H	2
GTP181L	2
GTT161G	2
GTT161K	2
GYE162Q	5
GYE182G	10
GYE182Q	10
GYE188C	2
GYE188D	2
GYE332Q	2
GYP182Q	2
HAA1H	2
HAA1L	2
HAA1T	10
HAA1V	10
HDGBD16	5
HDGBD16W	2
HDGBF18	2
HDGTC162Q	2
HDTAC2Q2Q	2
HSC2C	5
HSC2G	5
HSC2L	2
HSC2Q	10
LAC1TCE	2
LAC2QEE	2
LJCEG1T	10
LJCEG2Q	5
NCR182Q	5
PCC1T1T	10
PCC2Q1H	5
PGT1H1H	5
PTC1T1T	10
PTC2C2C	2
PTC2G2G	10
PTC2Q1T	2
PTC2Q2G	10
PTC2Q2Q	10
PTC2Q2QW	10
PTC2Q8C	2
PTC2Q9F	2
PTC8C1V	2
PTC8C8C	2
PTC8D8D	2
RDM522Q	5
RDM532Q	5
RJC532Q	5
RRC522Q	5
RRC532G	5
RRC532Q	5
RRH542Q	5
RRH562Q	2
SSC2C	5
SSC2G	10
SSC2L	5

SSC2Q	10
SSC2V	2
SSC3Q	5
SSC8C	2
SSC8D	2
SST1K	2
SST1T	5
SST1V	2
TAC1L1L	2
TAC1T1T	10
TAC1V1V	10
TAC2C2C	10
TAC2G1L	2
TAC2G1V	10
TAC2G2G	10
TAC2G2Q	2
TAC2L2L	10
TAC2Q1L	10
TAC2Q1V	10
TAC2Q2C	10
TAC2Q2G	10
TAC2Q2Q	10
TAC2Q2QW	10
TAC2Q8C	2
TAC2Q8D	2
TAC2Q8G	2
TAC2Q9F	2
TAC2Q9G	2
TAC2V2Q	5
TAC2V2V	10
TAC3D2Q	2
TAC3D3D	2
TAC3Q2Q	10
TAC3Q3Q	10
TAC8C8C	2
TAC8D8C	2
TAC8D8D	2
TAC8G8G	2
TAC9F9F	2
VBC1H	2
VBC1L	2
VBC1T	5
VBC1TV3C	5
VBC1V	10
VBC2C	5
VBC2G	10
VBC2L	5
VBC2Q	10
VBC2Q003	5
VFC1TV3C	10
VFC8C	2
VFR2Q	5
VSC1H	5
VSC1L	2
VSC1T	10
VSC1TV3C	10
VSC1V	10
VSC1VV3C	10
VSC2C	5
VSC2G	5
VSC2GV3C	10
VSC2L	5
VSC2Q	10
VSC2QV3C	10
VSC8C	2
VSC8D	2
VVR2Q	2
XAC2G2G	5
XAC2Q2Q	10
XBM2G2G	2
XBM2Q2Q	10
XBQ2G2G	2
XBQ2Q2Q	10
XBQ2Q2QW	2
XBQ2Q9F	2
XBV3Q3Q	2



Our powerful portfolio of brands:

nVent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER