

EGK020

Anti condensation small heater



Capacity (W)	20
L (mm)	60
Voltage (V)	120-240 V AC/DC
Starting current (A)	2.5
Weight (kg)	0.15
Item no.	EGK020

Description: Small semiconductor heater to be fixed in vertical position to prevent condensation. Mounting clip for 35 mm DIN rail (EN60715). For UL version please contact nVent HOFFMAN.

Heating element: PTC resistor.

Material: Plastic, and anodised aluminium profile.

Operating temperature: -45 °C to +70 °C. The heating capacity is for ambient temperature 20 °C.

Connection: 3 × 0.5 mm² (300 mm) silicon cable.
For UL heaters 3XAWG20 (300 mm) cable.

Protection: IP 44, Class I (earthed).

Approvals: CE, EAC.

Pack quantity: 1 piece.

This small anti-condensation heater, EGK, is available with a heating capacity range of 10-30 watts. Its size makes it easy to also in tight spaces. Water condensation is eliminated, also when the ambient temperature drops sharply. For UL version please contact nVent HOFFMAN.

CE EAC

IP 44