

# EHG045

Anti condensation large heater



Capacity (W)	45
L (mm)	65
Voltage (V)	110 - 250 V AC, 50/60 Hz
Starting current (A)	1.8
Weight (kg)	0.30
Item no.	EHG045

**Description:** Large heater to be fixed preferably in vertical position to prevent condensation. Mounting clip for 35 mm DIN rail (EN60715).

**Heating element:** PTC resistor, self regulating and temperature limiting.

**Material:** Plastic, and anodised aluminium profile.

**Operating temperature:** -40 °C to +70 °C. The heating capacity is for ambient temperature 20 °C.

**Connection:** Plug terminal connection (2 × 0.5-2.5 mm<sup>2</sup>), available on request with connecting cable (500 mm).

**Protection:** IP 20 supplied with terminals. IP 44 on request (supplied with cable).

**Approvals:** CE, EAC, cULus\_UL Listed.

**Pack quantity:** 1 piece.

This anti-condensation heater, EHG, is available with a heating capacity range of 15-150 watts. The wide range makes it easy to find the most optimum heater also when space within the enclosure is restricted. Water condensation is eliminated, also when the ambient temperature drops sharply.

CE EAC

IP20/44