

EL1200DS

LED Enclosure light with socket



Socket type	Type F (Shucko)
Operating voltage	100 V - 240 V ~, 50/60 Hz
Width	364

Description: LED enclosure light specially designed for nVent HOFFMAN enclosures. Fast and tool-free assembly thanks to a latching hook system designed to fit the 25mm hole pattern on nVent HOFFMAN enclosures. May be fitted horizontally or vertically.

Lamp type: LED.

Luminosity: 1200 lm.

Light colour: 4000 K (neutral white).

Power consumption: 12 W

Operating voltage: 100 V - 240 V ~, 50/60 Hz

Connection: Infeed, 3-pole. Through wiring, 3-pole.

Operating temperature: -20 °C ... +55 °C

Protection: IP20

Dimensions: 364 × 76 × 48 mm.

An innovative LED light specially designed for nVent HOFFMAN enclosures. Equipped with a socket. Tool-free assembly reduces the assembly time. Simple through wiring based on a plug and play system. Suitable for global use with wide range voltage 100-240V.

IP20