


SBF2C250

561172

CE IEC 60947-7-1
 430 A (IBSB70)
 1000 VAC / 1500 VDC
 Uimp = 12kV; Ipk = 42 kA
 Icw kA rms 1s = 14.4



UL 1953 AL or CU Conductor
 255 A IP20
 DLO: 175A 95% Fill Ratio
 1000 V AC/DC Halogen Free
 SCCR up to 100kA* UL 94 V-0



IEC 60947-7-1							
	No. Terminals	Conductor	Size	Ø DIA	Torque	Strip Length	Hex
	1	ERIFLEX FLEXIBAR** [ERIFLEX IBSB]	2X20X1 to 5X20X1 [50 to 70 mm ²]	N/A	31.1 N-m	29.5 mm	8 mm
	1 (Top)		35 mm ² to 120 mm ²	15.1 mm		29.5 mm	
	1 (Bottom)					55.3 mm	

UL 1953							
	No. Terminals	Conductor	Size	Ø DIA	Torque	Strip Length	Hex
	1	ERIFLEX FLEXIBAR** [ERIFLEX IBSB]	2X20X1 to 5X20X1 [50 to 70 mm ²]	N/A	275 in-lbs	1.16 in	5/16 in
	1 (Top)		6 AWG to 250 kcmil DLO: 6 to 2/0 AWG	0.594		1.16 in	
	1 (Bottom)					2.18 in	

- NOTE:
1. *Refer to UL file E497276.
 2. **Includes ERIFLEX FLEXIBAR Advanced
 3. For multiple phase assemblies, join blocks together before installing onto DIN profile.
 4. When mounted on DIN profile, end stops should be used on both ends of gangable blocks.
 5. For IEC, the cable must be secured within 15 cm of the terminal.

- WARNING:
1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
 2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
 3. All instructions must be completely followed to ensure proper and safe installation and performance.
 4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

SAFETY INSTRUCTIONS:
 All governing codes and regulations and those required by the job site must be observed.
 Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, CADDY, ERICO CADWELD, ERICO CRITEC, ERICO, ERIFLEX, and LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.