



IP 44,55 | TYPE 12 | IK 10

La gamma MKSL di armadi compatti in lamiera d'acciaio è disponibile sul mercato in diverse misure standard e rappresenta la soluzione ideale per le applicazioni di distribuzione di energia. L'apertura frontale può essere segregata con pannelli o porte parziali, soddisfacendo i requisiti dei sistemi di distribuzione di energia. La fornitura delle sole parti necessarie consente di ottenere piena flessibilità, costi ridotti e maggiore efficienza negli approvvigionamenti.

**Materiale:** Body: 1.35 mm painted steel. Rear and roof panels: 1.5 mm painted steel.

**Corpo:** Four times folded and seam-welded frame. Integrated double row hole pattern.

**Pannello posteriore:** Fitted by M6 torxscrews. Standard facilities for rear door mounting.

**Pannello superiore:** Removable.

**Messa a terra:** All panels are earthed through their fittings and are equipped with a separate earthingstud.

**Finitura:** RAL 7035 structured powder coating.

**Protezione:** IP 44, 55 | TYPE 12 | IK 10, depending of the doors configuration.

**Fornitura:** Body with rear panel and roof panel. Delivery also includes earthing bolts. Delivered on a pallet with identical width of the enclosure. All packing material is recyclable.

# MKSL-PD

Armadio semi-compatto | Alimentazione e distribuzione

A	L	P	Articolo n.
1800	600	400	MKSL18064R5
1800	800	400	MKSL18084R5
1800	1000	400	MKSL18104R5
1800	1200	400	MKSL18124R5
2000	600	400	MKSL20064R5
2000	800	400	MKSL20084R5
2000	1000	400	MKSL20104R5
2000	1200	400	MKSL20124R5

# MKSL-PD

Armadio semi-compatto | Alimentazione e distribuzione