

MKSL-PD

Semi-compact enclosure | Putere și distribuție



HOFFMAN

CONNECT AND PROTECT



IP 44,55 | TYPE 12 | IK 10

The mild steel compact floor standing enclosure range, MKSL is available off the shelf in many different sizes, and is ideal for power distribution applications. The front opening can be segregated with partial panels or doors to meet power distribution system requirements. Only parts required will be delivered, which means full flexibility, lower costs, and greater procurement efficiency will be achieved.

Material: Body: 1.35 mm painted steel. Rear and roof panels: 1.5 mm painted steel.

Corp: Four times folded and seam-welded frame. Integrated double row hole pattern.

Panou posterior: Fitted by M6 torxscrews. Standard facilities for rear door mounting.

Panou superior: Removable.

Împământare: All panels are earthed through their fittings and are equipped with a separate earthingstud.

Finisaj: RAL 7035 structured powder coating.

Protecție: IP 44, 55 | TYPE 12 | IK 10, depending of the doors configuration.

Livrare: Body with rear panel and roof panel. Delivery also includes earthing bolts. Delivered on a pallet with identical width of the enclosure. All packing material is recyclable.

MKSL-PD

Semi-compact enclosure | Putere și distribuție



CONNECT AND PROTECT

Dimensiuni dulap			
Î	L	A	Nr. articol
1800	600	400	MKSL18064R5
1800	800	400	MKSL18084R5
1800	1000	400	MKSL18104R5
1800	1200	400	MKSL18124R5
2000	600	400	MKSL20064R5
2000	800	400	MKSL20084R5
2000	1000	400	MKSL20104R5
2000	1200	400	MKSL20124R5

MKSL-PD

Semi-compact enclosure | Putere și distribuție



CONNECT AND PROTECT