

MKSL20084R5

Semi-compact enclosure | Floor Standing Enclosures



H	2000
W	800
D	400
Steps of 50 mm	36
Item no.	MKSL20084R5

Material: Body: 1.35 mm painted steel. Rear and roof panels: 1.5 mm painted steel.

Body: Four times folded and seam-welded frame. Integrated double row hole pattern.

Rear panel: Fitted by M6 torxscrews. Standard facilities for rear door mounting.

Roof panel: Removable.

Earthing: All panels are earthed through their fittings and are equipped with a separate earthingstud.

Finish: RAL 7035 structured powder coating.

Protection: IP 44,55 | TYPE 12 | IK 10, depending of the doors configuration.

Delivery: Body with rear panel and roof panel. Delivery also includes earthing bolts. Delivered on a pallet with identical width of the enclosure. All packing material is recyclable.

The mild steel compact floor standing enclosure range, MKSL is available off the shelf in many different sizes, and is ideal for power distribution applications. The front opening can be segregated with partial panels or doors to meet power distribution system requirements. Only parts required will be delivered, which means full flexibility, lower costs, and greater procurement efficiency will be achieved.

EAC

IP 44,55 | TYPE 12 | IK 10