

Single Pole Distribution Blocks Range



Part number	Article number	Max IEC Current	Line side : Nbre of connection	Line side Min and Max conductor size	Load side : Nbre of connection	Load side Min and Max conductor size	Depth	Height	Width
UD-80A	 569010	80 A	 1 Cable	6 - 16 mm ² #16 - # 4 AWG	 6 Cables	2.5 - 16 mm ² #16 - # 4 AWG	46 mm	69 mm	30 mm
UDJ-125A	 569020	125 A	 1 Cable	10 - 35 mm ² #8 - 1/0 AWG	 7 Cables	2.5 - 16 mm ² #14 - # 4 AWG	46 mm	77 mm	29 mm
UDJ-160A	 569030	160 A	 1 Cable	10 - 70 mm ² #8 - 3/0 AWG	 7 Cables	2.5 - 16 mm ² #14 - # 4 AWG	46 mm	77 mm	29 mm
UD-250A	 569040	250 A	 1 Cable	35 - 120 mm ² #6 AWG - 250 kcmil	 11 Cables	2.5 - 35 mm ² #14 - # 1 AWG	50 mm	96 mm	49 mm
UDF-250A	 569041	250 A	 Flat Conductor	Flexibar 3X9X0.8 - 6x15.5x0.8	 6 Cables	2.5 - 16 mm ² #14 - # 4 AWG	46 mm	79 mm	29 mm
UD-400A	 569050	400 A	 1 Cable	95 - 185 mm ² 3/0 AWG - 400 kcmil	 11 Cables	2.5 - 35 mm ² #14 - # 1 AWG	50 mm	96 mm	49 mm
UD-400112AL	 569252	400 A	 1 Cable	95 - 185 mm ² 3/0 AWG - 400 kcmil	 12 Cables	2.5 - 10 mm ² # 14 - # 6 AWG	50 mm	96 mm	55.73 mm
UD-400112CU	 569052	400 A	 1 Cable	96 - 185 mm ² 3/0 AWG - 400 kcmil	 12 Cables	2.5 - 10 mm ² # 14 - # 6 AWG	50 mm	96 mm	55.73 mm
UD-400212AL	 569251	400 A	 2 Cables	35 - 95 mm ² #8 - 3/0 AWG	 12 Cables	2.5 - 10 mm ² # 14 - # 6 AWG	50 mm	96 mm	55.73 mm
UD-400212CU	 569051	400 A	 2 Cables	35 - 95 mm ² #8 - 3/0 AWG	 12 Cables	2.5 - 10 mm ² # 14 - # 6 AWG	50 mm	96 mm	55.73 mm
UDF-500A	 569060	500 A	 Flat Conductor	Flexibar 4x15.5x0.8 - 8x24x1	 11 Cables	2.5 - 35 mm ² #14 - # 1 AWG	50 mm	96 mm	49 mm
UD6C500AL	 569201	500 A	 1 Cable	95 - 240 mm ² 3/0AWG- 500 kcmil	 6 Cables	10 - 50 mm ² #8 - 1/0 AWG	148.1 mm	90.2 mm	43.7 mm
UDF6C500AL	 569202	500 A	 Flat Conductor	Flexibar 2x20x1 - 10x24x1 IBS/IBSB 50 - 100 mm ²	 6 Cables	10 - 50 mm ² #8 - 1/0 AWG	148.1 mm	90.2 mm	43.7 mm
UDF9C500AL	 569204	500 A	 Flat Conductor	Flexibar 2x20x1 - 10x24x1 IBS/IBSB 50 - 100 mm ²	 9 Cables	4 - 25 mm ² #12 - # 4 AWG	127 mm	78 mm	43.7 mm
UDF12C500AL	 569206	500 A	 Flat Conductor	Flexibar 2x20x1 - 10x24x1 IBS/IBSB 50 - 100 mm ²	 12 Cables	4 - 25 mm ² #12 - # 4 AWG	127 mm	78 mm	43.7 mm
UD9C630AL	 569203	630 A	 1 Cable	120 - 300 mm ² 4/0 AWG- 600 kcmil	 9 Cables	4 - 25 mm ² #12 - # 4 AWG	127 mm	78 mm	43.7 mm
UD2C12C630AL	 569205	630 A	 2 Cables	95 - 185 mm ² 3/0 AWG - 400 kcmil	 12 Cables	4 - 25 mm ² #12 - # 4 AWG	127 mm	78 mm	43.7 mm
UDF12C800AL	 569208	800 A	 Flat Conductor	Flexibar 2x20x1 - 10x32x1 IBS/IBSB 50 - 240 mm ²	 12 Cables	4 - 25 mm ² #12 - # 4 AWG	147.3 mm	79.8 mm	55.2 mm
UD2C12C1000AL	 569207	1000 A	 2 Cables	35 - 240 mm ² 2 AWG - 500 kcmil	 12 Cables	4 - 25 mm ² #12 - # 4 AWG	147.3 mm	79.8 mm	55.2 mm
UDF9C1000AL	 569210	1000 A	 Flat Conductor	Flexibar 6x24x1 - 10x50x1 IBS/IBSB 120 - 240 mm ²	 9 Cables	10 - 95 mm ² #8 - 3/0 AWG	195.6 mm	105.9 mm	70.5
UD2C9C1250AL	 569209	1250 A	 2 Cables	185 - 400 mm ² 400 kcmil - 750 kcmil	 9 Cables	10 - 95 mm ² #8 - 3/0 AWG	195.6 mm	105.9 mm	70.5