

CONTROL PANEL FOR PIPE FROST PROTECTION OF SPRINKLER SYSTEMS



DESCRIPTION

The nVent RAYCHEM SBS-XX-SNR control panel for pipe frost protection of sprinkler systems provides a totally integrated solution for the control of RAYCHEM self-regulating heating cables for sprinkler applications. The control panel comprises multi-control and multi-sensor thermostatic control and redundant circuit automatic switching capability in order to be compliant with the requirements of BS EN 12845:2008. The SBS-xx-SNR panels can switch 2-12 circuits of frost protection heating cables with up to 12 control and sensor inputs (1 per "prime" circuit and redundant circuit). The panel also includes electrical circuit protection devices (C-type circuit breakers and RCD protection) for safety and peace of mind. The panels need only be connected to the 400Vac (3 phase) supply.

ADVANTAGES

Fast connection of multiple circuits directly into the control panel

- No need for additional connections or junction boxes
 - 2-12 maximum circuit lengths can be connected to 1 panel
 - Automatic redundant circuit switching as required by BS EN 12845:2008
 - Circuit protection and safety devices integrated into the panel
- No need for separate safety devices
 - Digital temperature feedback for each individual sprinkler line
 - Alarm function in case of heater failure (and automatic switch to redundant line)
 - Complete system from the manufacturer
- System and components specifically selected for high performance frost protection of sprinkler systems

TECHNICAL DATA

Control	2 x Elreha Tarn 1170 Digital line sensing control per sprinkler line - Prime circuit - Redundant circuit (max. 12 controllers per panel)
Supply voltage	400 Vac (3 Phase)
Heater circuit voltage	230Vac 50/60Hz
Ambient temperatures	+10°C to +35°C
Sensor	Ambient sensor and line sensor per sprinkler line
Approval	CE (IEC61439)
Main switch	Dependent on selected panel (32A - 63A)
RCD	300mA
Line Circuit breakers	16A (Type C) per heating circuit.
Alarm function	1 general potential free alarm contact; Alarm light indicator on panel front
Selector switch	Automatic Mode/ Manual Prime circuit on mode / Manual redundant circuit on mode

PANEL DIMENSIONS

Product	Weight (kg)	Length (mm)	Width (mm)	Depth (mm)
SBS-02-SNR	45	600	600	210
SBS-04-SNR	90	800	800	210
SBS-06-SNR	90	800	800	210
SBS-08-SNR	115	1000	800	300
SBS-10-SNR	140	1000	1000	300
SBS-12-SNR	140	1000	1000	300

RELATED PRODUCTS

The SBS-xx-SNR control panel is compatible with the RAYCHEM pipe frost protection cables:

FS-A-2X - 150 metres per circuit

FS-B-2X - 105 metres per circuit

FS-C10-2X - 150 metres per circuit

(for 180m circuits, please contact nVent RAYCHEM)

R-ETL-A - 100 meters per circuit

ORDER REFERENCE

Product name	Order reference	Description
SBS-02-SNR	185780-000	Multi circuit control panel for sprinkler systems (1 pipe)
SBS-04-SNR	278362-000	Multi circuit control panel for sprinkler systems (2 pipes)
SBS-06-SNR	300074-000	Multi circuit control panel for sprinkler systems (3 pipes)
SBS-08-SNR	158834-000	Multi circuit control panel for sprinkler systems (4 pipes)
SBS-10-SNR	012276-000	Multi circuit control panel for sprinkler systems (5 pipes)
SBS-12-SNR	712998-000	Multi circuit control panel for sprinkler systems (6 pipes)

INSTALLATION INSTRUCTION

Complete panel wiring information and schematics are provided with the product. All electrical installations must be carried out by an approved electrician in compliance with local electrical requirements and norms.

United Kingdom

Tel 0800 969 013
Fax 0800 968 624
salesthermalUK@nvent.com

Ireland

Tel 1800 654 241
Fax 1800 654 240
salesIE@nvent.com

South East Asia

Tel +65 67685800
Fax +65 67322263

Australia

Tel +61 2 97920250
Fax +61 2 97745931

India- Noida

Tel +91 120 464 9500
Fax +91 120 464 9548
NTMinfome@nvent.com

India - Mumbai

Tel +91 22 6775 8800/01
Fax +91 22 2556 1491
NTMinfome@nvent.com

UAE

Tel +971 4 378 1700
Fax +971 4 378 1777
NTMinfome@nvent.com



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER