
XMI-JB



HAZARDOUS LOCATION CAST ENCLOSURE FOR MI HEATING UNITS IN CID1 APPLICATIONS



PRODUCT OVERVIEW

Hazardous area (CID1) or ordinary area applications

MI power connection box

MI splice connection box

Enables conduit connection for power supply

Provides easy access to terminations for maintenance and future system changes

RTD connection box

CONSTRUCTION

- Aluminum Body and Cover (Copper-free aluminum (less than 4/10 of 1%)
- · Electrostatically applied powder coating finish
- External threaded body provides additional wiring room, cover opening 3 1/2" (89 mm)
- Smooth, rounded integral bushing in each hub protects conductor insulation
- Cover and gasket furnished with box as standard, Type 4X
- 5 x ³/₄" threaded hub locations (One in base, 4 on sides)
- 3 x ³/₄" close up plugs
- 2 reducer bushings 3/4" x 1/2"
- Two cast in mounting lugs
- Dimensions: 4 ½" x 3 ½" (114 x 89 mm)

APPROVALS

Class I, Div.1 (Zone 1) & Div. 2 (Zone 2), Groups B, C, D Class II, Div. 1 & 2, Groups E, F, G Class III Enclosure Type: Type 4X

ELECTRICAL SPECIFICATIONS

Green ground screw


4 pole terminal strip (CSA-600 Vac, 65 A, 18–6 AWG /UL-300 Vac, 65 A, 18–6 AWG) Maximum operating voltage 600Vac


Power cable gland not included

Space to tap an external bonding connection - when a metal junction box is used for MI splices, a bonding conductor is required

ENCLOSURE DETAIL

XMI-JB							
Catalog Number	Hub Size	Dimensions A B C D				Cover Opening	Volume CU. in.
XMI-JB	³ /4"	4 ¹ / ₂ " (114 mm)	2 ³/ ₈ " (60 mm)	3 ¹ / ₂ " (89 mm)	¹¹ / ₁₆ " (17 mm)	3 ¹ / ₂ " (89 mm)	25





XMI-JB


ORDERING DETAILS

Description	Catalog number	Part number	Weight/lbs
Enclosure	XMI-JB	XMI-JB	3.5lbs

XMI-JB

Spare Parts and Accessories

Terminal Strip	4POLETSTRIP	4POLETSTRIP	0.1lbs
 4 pole terminal strip (CSA-600 Vac, 65 A, 18-6 AWG /UL-300 Vac, 65 A, 18-6 AWG) for use with XMI-JB enclosure 			
May be used for additional RTD connections			



Reducer Bushing PTRDBH3412 PTRDBH3412 0.1 lbs Zinc plated steel reducer bushing for use with XMI-JB enclosure • Reduces 34" NPT tapered hole to 1/2" NPT • Body length 23/32" (18 mm) • Class I, Div. 1 & 2, Groups A,B,C,D • Class I, Zone 1, Groups IIC, IIB, IIA • Class II, Div 1 & 2, Groups E,F,G Support Bracket UMB 263757-000 1.0 lbs • Pipe mounted support bracket • Material: 304 stainless steel • Accommodates 3" (76 mm) of insulation • Order pipe strap separately (allow 1 1/2" (40 mm) extra length on strap)

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 info@nvent.com

Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.info@nvent.com

Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 info@nvent.com



Our powerful portfolio of brands: **nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners Vent reserves the right to change specifications without notice.