












EB168
568630



-  Metric rigid stranded cable
-  Metric flexible stranded cable
-  AWG solid cable
-  AWG stranded cable

IEC®					
#	Conductor	Size	Ø		Strip Length
1		1.5 - 4mm ²	0.18in [4.5mm]	13 in-lbs [1.5 N.m]	0.50in [12.7mm]
		0.75 - 4mm ²			
UL®					
#	Conductor	Size	Ø		Strip Length
1		16 - 10 AWG	0.18in [4.5mm]	17 in-lbs [2 N.m]	0.50in [12.7mm]
		14 - 10 AWG			

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

WARNING:

1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

TECHNICAL SUPPORT
www.nVent.com

IP8056_C

1 OF 1

© 2008-2019 nVent All Rights Reserved

