# QuickNet 90



# **COMFORT YOU DESERVE**



#### **PRODUCT DESCRIPTION**

Self adhering, low profile floor heating mat for installation immediately under ceramic tiles or natural stone.

nVent RAYCHEM QuickNet 90 is sold as complete pack consisting of a pre-terminated floor heating cable installed on a fiber glass mat and a SENZ WIFI timer thermostat.

QuickNet 90 is the ideal floor heating system to increase the comfort at home and in the office as well as in your showroom or entrance hall.

QuickNet 90 can also be installed under wooden or engineered wooden floors.



#### **ADVANTAGES**

#### The design phase

Ideal heating system during early autumn or spring time as well as the perfect complementary heating system (for example in bathroom as additional heating to a towel dryer)

Extremely low installation height ca. 3,5 mm

Ideal for renovation

Can be used in shower areas

Compatible with all stable subfloors e.g. concrete, anhydrite, plaster, ceramic subfloor

Following floorings can be applied: Tiles, marble, stones: max. 30 mm thickness

Parquet floors, engineered wood or vinyl floors with maximal

thermal resistance (R-value) of 0,15 m<sup>2</sup>K/W

#### The installation phase

Fast and easy due to self adhering mat


Due to the low profile no issue with heights of existing doors neither with floor level of existing stairs  $\,$ 

Due to the dual conductor cable only one cold lead connection which enables easy lay-out and installation of the mats

Several heating mat sizes available to fit in all the rooms

Cable easily detachable from the mat with only 2 cuts in the mat. Loose cable can then be used to go around obstacles.

Cable is protected by the mat during installation phase



# The application

Ideal heating for comfort in your bathroom, kitchen and conservatory

Extra low energy consumption and possibility to control and monitor from a distance with the WIFI enabled and EcoDesign compliant touchscreen SENZ WIFI timer thermostat

No measurable electro-magnetic fields due to the dual conductor heating cable

Long life and maintenance free



# **TECHNICAL DATA**

Nominal power 90 W/m<sup>2</sup> 230 Vac Voltage 90°C Max. Exposure Temperature Min. Installation Temperature +5°C

Heating cable Low smoke, zero halogen

Cold lead 1x 2,5 m cold lead; Cross section 3 x 1,0 mm<sup>2</sup>

Mat Self adhering fiber glass mat Wet room Approved; ELCB 30mA required

Circuit breaker C13 A with max heating mat surface till 33 m<sup>2</sup>

Approvals **VDE** 

**SEMKO** CE

#### **RELATED NVENT RAYCHEM PRODUCTS**

#### **SENZ WIFI**

SENZ WIFI is top class WIFI enabled Touchscreen thermostat with the following features:

- · Energy Efficient and EcoDesign compliant:
  - Electronic room temperature control with weekly schedule
  - Adaptive start control
  - Open window detection
  - Distance control and monitoring
- · Ease of installation:
  - Intuitive setup-wizard
- · APP controlled from anywhere:
  - Programming the 3 Economic modes has never been easier than through an APP
  - Switching between program modes can be done from anywhere with the APP
  - Temporary adjustments on the normal schedule like BOOSTING the temperature for desired period of time or overriding the schedule until the next scheduled event
  - Controlling the entire home (up to 32 zones) with the APP
  - Holiday mode is combining the best of both worlds lowering down energy consumption while adding a high level of comfort. Your floor will be back at comfortable temperature right before you enter the home

#### **REFERENCE NUMBER**

QUICKNET 90					
Product Name	Without thermostat	With SENZ WIFI thermostat	Area	Output	Dimensions (W x L in m)
R-QN-N-1,0M2	SZ18300279	SZ18300429	1	90	0,5 x 2,0
R-QN-N-1,5M2	SZ18300280	SZ18300430	1.5	135	0,5 x 3,0
R-QN-N-2,0M2	SZ18300281	SZ18300431	2	180	0,5 x 4,0
R-QN-N-2,5M2	SZ18300282	SZ18300432	2.5	225	0,5 x 5,0
R-QN-N-3,0M2	SZ18300283	SZ18300433	3	270	0,5 x 6,0
R-QN-N-3,5M2	SZ18300284	SZ18300434	3.5	315	0,5 x 7,0
R-QN-N-4,0M2	SZ18300285	SZ18300435	4	360	0,5 x 8,0
R-QN-N-4,5M2	SZ18300286	SZ18300436	4.5	405	0,5 x 9,0
R-QN-N-5,0M2	SZ18300287	SZ18300437	5	450	0,5 x 10,0
R-QN-N-6,0M2	SZ18300288	SZ18300438	6	540	0,5 x 12,0
R-QN-N-7,0M2	SZ18300289	SZ18300439	7	630	0,5 x 14,0
R-QN-N-8,0M2	SZ18300290	SZ18300440	8	720	0,5 x 16,0
R-QN-N-9,0M2	SZ18300291	SZ18300441	9	810	0,5 x 18,0
R-QN-N-10,0M2	SZ18300292	SZ18300442	10	900	0,5 x 20,0
R-QN-N-12,0M2	SZ18300293	SZ18300443	12	1080	0,5 x 24,0

#### **SUBFLOOR PREPARATION**

The subfloor should be clean, stable and rigid, without cracks or adhesion-reducing substances. Large cracks in the subfloor should be filled prior to laying the mat.

Uneven surfaces will need to be levelled prior to installation. With cement plaster and anhydrite plaster, one should ensure that the substance has dried sufficiently according to the applicable norms. Anhydrite plaster should be smoothened and dust free. With quickly solidifying plaster, one should follow the suppliers instructions.

Apply a layer of tile glue primer (dependent on subfloor) to the floor before installing the mat to ensure good adhesion of the QuickNet to the subfloor.

The heating cable should not be installed under bath tubs, shower cabins, surface covering furniture, etc. The heating cable should not be installed where holes will be drilled in the floor.


Applicable norms, rules and data sheets as well as instructions and manuals are to be followed!

## INSTALLATION INSTRUCTION

The QuickNet cold lead is inserted in a flexible tubing and connected to the connection box. QuickNet 90 shall allways be controlled by an electric underfloor heating thermostat with external floor sensor and compliant with the EcoDesign directive (like the NRG-DM, GREEN LEAF or SENZ WIFI). The thermostat sensor, which is also protected in a flexible tubing (3m included with R-QN-N), is positioned centrally between two heating cable runs and as close as possible to the final floor covering.


QuickNet 90 can be used under tiles and natural stone. The mat can even be embedded directly in the tile glue (in that case make sure it is embedded in at least 5mm of tile glue).

#### FLOOR CONSTRUCTION FOR TILE OR NATURAL STONE



#### Fig A:

- 1 Floor covering (can be tile or natural stone)
- 2 Tile glue
- 3 (Waterproofing layer optional for shower areas)
- 4 (Filler material Optional)
- 5 QuickNet + Floor sensor inserted in sensor tube
- 6 Primer
- 7 Sub floor
- 8 Insulation
- Bearing construction




#### Fig B:

- 1 Floor covering (can be tile or natural stone)
- 2 Tile glue
- 3 (Waterproofing layer optional for shower areas)
- 4 (Filler material Optional)
- 5 QuickNet + Floor sensor inserted in sensor tube
- 6 Primer
- 7 Gypsum plasterboard ≥13mm
- 8 Wooden plate
- 9 Joist and insulation layer between the joists


QuickNet 90 can be installed under parquet floors, engineered wooden floors or laminate floors. It then needs to be embedded in a minimum of 15mm of filler material.

# FLOOR CONSTRUCTION FOR PARQUET, LAMINATE OR ENGINEERED WOOD



# Fig C:

- 1 Floor covering (Parquet floor)
- 2 Glue
- 3 (plywood Optional)
- 4 Filler material (between 15 and 30mm of filler material)
- 5 QuickNet + Floor sensor inserted in sensor tube
- 6 Primer
- 7 Sub floor
- 8 Insulation
- Bearing construction



#### Fig D:

- 1 Floor covering (Engineered wood installed floating)
- 2 Foam underlayement
- 3 Filler material (between 15 and 30mm of filler material)
- 4 QuickNet + Floor sensor inserted in sensor tube
- 5 Primer
- 6 Sub floor
- 7 Insulation
- 8 Bearing construction

For detailed installation instructions refer to SZ12300106 - IM-EU1252.

# **United Kingdom**

Tel 0800 969 013 Fax 0800 968 624 salesthermalUK@nVent.com

# India - Noida

Tel +91 120 464 9500 Fax +91 120 464 9548 NTMinfome@nVent.com

#### Ireland

Tel 1800 654 241 Fax 1800 654 240 salesIE@nVent.com

# India - Mumbai

Tel +91 22 6775 8800/01 Fax +91 22 6775 8997 NTMinfome@nVent.com

#### **South East Asia**

Tel +65 67685800 Fax +65 67322263

# **UAE**

Tel +971 4 378 1700 Fax +971 4 378 1777 NTMinfome@nVent.com

# **Australia**

Tel +61 2 97920250 Fax +61 2 97745931



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER